



Scan for full manual

T-1GD Quick Start Guide

This guide helps you install and use your **T-1GD** for the first time.

Go to www.kramerav.com/downloads/T-1GD to download the latest documentation.

Step 1: Check what's in the box


- ✓ T-1GD 1 Gang bracket
- ✓ 2 M3x6 screws
- ✓ 2 M3x5 flat-head screws
- ✓ 1 Quick start guide

Step 2: Install the T-1GD


Use **T-1GD** for installing a Kramer 1 gang US-D size wall plate in a TBUS with a **dual power socket** opening frame.

To connect the T-1GD:


1. Attach the faceplate of the wall plate.




2. Use the two M3x6 screws (supplied with the kit) to attach T-1GD to the wall plate.



- Place **T-1GD** under the dual power socket opening and tighten with the two M3x5 screws (supplied with the kit).



The frame can now be mounted onto the TBUS.



Specifications

| | | |
|--------------------------|-------------------------------|--|
| Environmental Conditions | Operating Temperature | 0° to +40°C (32° to 104°F) |
| | Storage Temperature | -40° to +70°C (-40° to 158°F) |
| | Humidity | 10% to 90%, RHL non-condensing |
| General | Net Dimensions (W, D, H) | 12.3cm x 5cm x 0.75cm (4.8" x 2" x 0.3") |
| | Shipping Dimensions (W, D, H) | 14.5cm x 9.6cm x 6.2cm (5.7" x 3.8" x 2.4") |
| | Net Weight | 0.06kg (0.13bs) approx. |
| | Shipping Weight | 0.1kg (0.2lbs) approx. |